



ASR 35 H ACP with Electromagnetic Shaking and Measurement of Pressure Differentials

- Ideal vacuum cleaner for removal of mould and old insulation in roof and wall areas
- Ideal when sanding painted or coated wood surfaces with lead, nickel, cadmium or chromium content
- Compact vacuum cleaner for liquids and dry solids with commercial registration
- Power socket for a power tool for using the automatic-start-up/shut-down of the vacuum cleaner
- AutoCleanPlus: saves both costs and time thanks to automatic MPulse filter cleaning during continuous use
- If the optimum suction performance falls below a certain level, the filters are vibrated immediately
- Maximum user protection: certified in accordance with EU standard for H class dusts
- Automatic shut-down when vacuuming liquids once the maximum fill level is reached
- Warning signal on shortfall of the minimum volume flow to protect the user
- Optimum suction power by preselection of the hose diameter
- Automatic trailing mechanism for emptying the suction hose completely
- Antistatic basic equipment prevents static charge when using appropriate accessories
- Sturdy thanks to especially large wheels and castors with wheel stop
- Cable winding mechanism
- Practical accessory case and storage area

Order no.	602059000
EAN code	4007430279316
Air output max.	4380 l/min / 157 cfm
Vacuum	270 hPa (mbar) / 3.6 psi
Filter surface	8600 cm ² / 1333 sq.inch
Input power max.	1400 W
Container volume	35 l / 9 gal
Suction hose Ø	35 mm / 1 3/8 "
Hose length	4 m / 15 ft
Weight	16 kg / 35.3 lbs
Cable length	8 m / 26 ft

Scope of delivery

Antistatic suction hose (Ø 35 mm / 4 m), Connection bush Ø 41/48 mm, Handle adapter, 2 Plastic suction tubes, 2 HEPA polyester filter cassettes, PE Disposal bag, Crevice nozzle, Floor nozzle (300 mm wide)