



ASR 35 L ACP with Electromagnetic Shaking and Measurement of Pressure Differentials

- For extraction from the power tool in continuous mode, both on construction sites and in the workshop
- Especially suited for extracting concrete and rock dust
- Compact vacuum cleaner for liquids and dry solids with commercial registration
- AutoCleanPlus: saves both costs and time thanks to automatic MPulse filter cleaning during continuous use
- If the optimum suction performance falls below a certain level, the filters are vibrated immediately
- User protection: certified in accordance with EU standard for L class dust
- Automatic shut-down when vacuuming liquids once the maximum fill level is reached
- Suction power control for adapted suction performance
- Automatic trailing mechanism for emptying the suction hose completely
- Antistatic basic equipment prevents static charge when using appropriate accessories
- Sturdy thanks to especially large wheels and castors with wheel stop
- Cable winding mechanism
- Practical accessory case and storage area

Order no.	602057000
EAN code	4007430250094
Air output max.	4380 l/min / 157 cfm
Vacuum	270 hPa (mbar) / 3.6 psi
Filter surface	8600 cm ² / 1333 sq.inch
Input power max.	1400 W
Container volume	35 l / 9 gal
Suction hose Ø	35 mm / 1 3/8 "
Hose length	3.2 m / 11 ft
Weight	16 kg / 35.3 lbs
Cable length	8 m / 26 ft

Scope of delivery

Suction hose (Ø 35 mm / 3.2 m), Handle adapter, 2 Plastic suction tubes, 2 Polyester filter cassettes (M class), PE Filter bags, Crevice nozzle, Floor nozzle (370 mm wide)