



SE 17-200 RT Set

- Powerful burnishing machine for sanding, satin-finishing, brushing and high-gloss polishing of e.g. stainless steel
- Maximum productivity thanks to powerful 1,700 Watt motor and high-performance planetary gear train
- Perfect ergonomics thanks to slim handle area for optimal guidance and low-fatigue working
- Metabo Marathon motor with patented dust protection for long service life
- Vario-Tacho-Constamatic (VTC)-Full Wave Electronics with Thumbwheel: for working at customised speeds to suit the application material and speeds that remain almost constant, even under load
- Spindle lock and tool-free flange nut for fast accessory change
- Fast and tool-free adjustment of guard and side handle
- Smooth-running, form-fit mounting arbor for a uniform grinding result
- Overload protection: protects the motor from overheating
- Electronic soft start for smooth start-up
- Restart protection: prevents unintentional start-up after power supply interruption
- Auto-stop carbon brushes to protect the motor

Order no.	602259500
EAN code	4007430323552
Rated input power	1700 W
Output power	1070 W
Torque	17 Nm / 151 in-lbs
No-load speed	800 - 3000 rpm
Spindle thread	M 14
Abrasive tool diameter	100 - 200 mm // 4 - 8 "
Abrasive tool width	50 - 100 mm // 2 - 4 "
Weight (without power cable)	2.9 kg / 6.4 lbs
Cable length	4 m / 13 ft

Scope of delivery

Side handle, 1 Expansion roller (Ø90x100mm), 3 Sanding belts (Ø90x100mm; P80), 1 Fleece grinding wheel (Ø105x100mm; P280), 1 Flap wheel (Ø105x100mm; P80), 1 Flap / fleece grinding wheel (Ø105x100mm; P180), Metal carry case