



## SSW 18 LTX 400 BL

- Unique Metabo brushless motor for quick work progress and highest efficiency for any application
- Overload protection: protects the motor from overheating
- High torque accompanied by an exceptionally compact design
- Low kick-back operation with extremely high torque
- Twelve speed/torque levels for a wide range of applications
- Integrated work light for illumination of the work area
- Robust die cast aluminium gear housing for optimum heat dissipation and durability
- Handy belt hook, can be fixed either on the right or left side
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: [www.cordless-alliance-systems.com](http://www.cordless-alliance-systems.com)

Order no.	602205890
EAN code	4007430244284
Battery voltage	18 V
Max. screw size	M20
Max. no-load speed	0 - 2150 rpm
Maximum impact rate	4250 bpm
Maximum torque	400 Nm / 295 ft. lbs
Max. loosening torque	620 Nm / 420 ft. lbs
Speed/torque levels	12
Bit retainer	Male square 1/2" (12.70 mm)
Weight without battery pack	1.3 kg / 2.9 lbs
Weight with battery pack	1.8 kg / 4 lbs

### Scope of delivery

Belt Hook, without battery pack, without charger