



## GB 18 LTX BL Q I

- High-grade cordless drill/screwdriver with unique, patented thread-tapping function
- Quick and interruption-free cutting and cleaning of threads thanks to automatic change of direction of rotation
- Quick-change tapping chuck for inserting taps with square and cylindrical shanks
- Long service life and tool life of the tappers by virtue of intelligent torque monitoring
- Metabo "Quick" System: quick change of bit retainer and bits for flexible working
- Unique Metabo brushless motor for quick work progress and highest efficiency when drilling and screwdriving
- Selectable "impuls" mode for removal of stubborn screws and for spot-drilling on smooth surfaces
- Precision Stop: electronic torque control with increased precision for accurate and intricate working
- Overload protection: protects the motor from overheating
- Electronic safety shutdown: no kickback if the drill bit stops unexpectedly - for high user safety
- Handy belt hook and bit holder can be fixed either on the right or left side
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: [www.cordless-alliance-systems.com](http://www.cordless-alliance-systems.com)

Order no.	602362840
EAN code	4061792188204
Battery voltage	18 V
Maximum torque - soft	65 Nm / 575 in-lbs
Pulse torque	65 Nm / 575 in-lbs
Maximum torque, hard	130 Nm / 1151 ft. lbs
Adjustable torque	1 - 20 Nm // 9 - 177 in-lbs
Max. thread diameter	M 12 (1/2" UNC/ UNF)
Drill Ø steel	13 mm / 1/2 "
Drill-Ø soft wood	68 mm / 2.68 "
No-load speeds	0 - 550 / 0 - 2000 rpm
Chuck capacity	1.5 - 13 mm // 1/32 - 1/2 "
Weight without battery pack	1.8 kg / 4 lbs
Weight with battery pack	2.2 kg / 4.9 lbs

### Scope of delivery

Quick-change tapping chuck M4-M6, Quick-change tapping chuck M8-M12, Side handle, Belt hook and bit case, metaBOX 145 L