



## SB 18 LT BL

- Brushless cordless hammer drill with optimal power for demanding applications
- Unique Metabo brushless motor for quick work progress and highest efficiency when drilling and screwdriving
- High-performance impact mechanism for optimum drilling performance
- Integrated working light to illuminate the contact area
- With handy belt hook and bit case which can be fixed either on the right or left side
- With metaBOX, the intelligent solution for transport and storage
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: [www.cordless-alliance-systems.com](http://www.cordless-alliance-systems.com)

Order no.	602316840
EAN code	4007430297808
Type of battery pack	Li-Power
Battery voltage	18 V
Maximum torque - soft	34 Nm / 301 in-lbs
Maximum torque, hard	75 Nm / 663.8 in-lbs
Adjustable torque	0.7 - 8 Nm // 6 - 71 in-lbs
Drill-Ø masonry	13 mm / 1/2 "
Drill Ø steel	13 mm / 1/2 "
Drill-Ø soft wood	38 mm / 1 1/2 "
No-load speed	0 - 600 / 0 - 2100 rpm
Maximum impact rate	31950 bpm
Chuck capacity	1.5 - 13 mm // 1/16 - 1/2 "
Weight without battery pack	1.2 kg / 2.6 lbs
Weight with battery pack	1.6 kg / 3.5 lbs

### Scope of delivery

Keyless chuck, Belt hook and bit case, metaBOX 145, without battery pack, without charger