



BS 18 LTX BL I

- Brushless drill/screwdriver with maximum power for demanding applications
- Selectable "impuls" mode for removal of stubborn screws and for spot-drilling on smooth surfaces
- Unique Metabo brushless motor for quick work progress and highest efficiency when drilling and screwdriving
- Precision Stop: electronic torque control with increased precision for accurate and intricate working
- Overload protection: protects the motor from overheating
- Electronic safety shutdown: no kickback if the drill bit stops unexpectedly - for high user safety
- Integrated LED work light with night light function for optimal brightness in the work area
- Handy belt hook and bit holder can be fixed either on the right or left side
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	602358840
EAN code	4061792188143
Battery voltage	18 V
Maximum torque - soft	65 Nm / 575 ft. lbs
Pulse torque	65 Nm / 575 in-lbs
Maximum torque, hard	130 Nm / 1151 ft. lbs
Adjustable torque	1 - 20 Nm // 9 - 177 in-lbs
Drill Ø steel	13 mm / 1/2 "
Drill-Ø soft wood	68 mm / 2.68 "
No-load speeds	0 - 550 / 0 - 2000 rpm
Chuck capacity	1.5 - 13 mm // 1/16 - 1/2 "
Weight without battery pack	1.7 kg / 3.7 lbs
Weight with battery pack	2.2 kg / 4.9 lbs

Scope of delivery

Keyless chuck, Bit holder, Side handle, Belt hook and bit case, metaBOX 145 L