



SSW 18 LTX 1450 BL

- Extremely powerful cordless impact driver with 1/2" male square and 1450 Nm
- Unique Metabo brushless motor for quick work progress and highest efficiency for any application
- Loosening in APS mode (automatic power shift): prevents falling of the screw/nut with automatic speed reduction after loosening
- Overload protection: protects the motor from overheating
- Very powerful for demanding applications
- Low kick-back operation with extremely high torque
- Twelve speed/torque levels for a wide range of applications
- Integrated work light for illumination of the work area
- Robust die cast aluminium gear housing for optimum heat dissipation and durability
- Many brands, one battery pack system: This product can be combined with numerous 18 V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	602401850
EAN code	4061792202412
Battery voltage	18 V
Max. screw size	M30
Max. no-load speed	0 - 1500 rpm
Maximum impact rate	2250 bpm
Maximum torque	1450 Nm / 12833 in-lbs
Max. loosening torque	1900 Nm
Speed/torque levels	12
Bit retainer	Male square 1/2" (12.70 mm)
Weight without battery pack	2.9 kg / 6.4 lbs

Scope of delivery

without battery pack, without charger