



SB 18 LTX-3 BL Q I

- Brushless 3-speed cordless hammer drill with maximum power, ideal for demanding metal applications
- Third speed setting with high torque (max. 4,000/min) for extended range of application and even faster drilling progress, especially in metal
- Hammer drill function for drilling in masonry
- Metabo QuickPlus System: quick change of bit retainer and bits, for flexible working with maximum load
- Selectable "impuls" mode for removal of stubborn screws and for spot-drilling on smooth surfaces
- Precision Stop: electronic torque control with increased precision for precise, delicate working
- Overload protection: protects the motor from overheating
- Electronic safety shutdown: no kickback if the drill bit stops unexpectedly - for high user safety
- With handy belt hook and bit case which can be fixed either on the right or left side
- With metaBOX, the intelligent solution for transport and storage
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	603185840
EAN code	4061792225251
Battery voltage	18 V
Maximum torque - soft	65 Nm / 575.3 in-lbs
Maximum torque, hard	130 Nm / 1150.6 in-lbs
Adjustable torque	1 - 18 Nm // 8.9 - 159.3 in-lbs
Drill-Ø masonry	16 mm / 5/8 "
Drill Ø steel	16 mm / 5/8 "
Drill-Ø soft wood	68 mm / 2.68 "
No-load speed	0 - 450 / 0 - 2000 / 0 - 4000 rpm
Maximum impact rate	38000 bpm
Chuck capacity	1.5 - 13 mm // 1/16 - 1/2 "
Weight without battery pack	2 kg / 4.4 lbs
Weight with battery pack	3 kg / 6.6 lbs

Scope of delivery

Futuro Plus quick-change chuck "QuickPlus", Side handle, metaBOX 145 L, without battery pack, without charger