



RFEV 19-125 RT with milling head pointed

- For effective removal of plaster, adhesive residues, soft screed and old paint from walls, ceilings and floors
- Maximum productivity thanks to top 1,900 Watt with low weight
- Double reduction high-performance gearing for maximum torque and high output
- Fast work progress thanks to large milling diameter
- Perfect ergonomics thanks to slim handle for maximum control and easy working overhead
- Cutting depth can be adjusted easily and without the need for tools
- Robust protective cover made from die-cast aluminium with spring-mounted brush rim for low-dust working
- Front handle for safe and uniform guidance when milling, adjustable without tools
- Can be used as renovation grinder on smaller areas when using a diamond cup wheel
- Vario Tacho Constamatic (VTC) Full-wave Electronics with Thumbwheel: for working at customised speeds to suit the application material and speeds that remain almost constant, even under load
- Electronic soft start for smooth start-up
- Restart protection: prevents unintentional start-up after power supply interruption
- Connection for dust extraction \varnothing 35/41 mm

| Order no. | 603826710 |
|------------------------------|-----------------------|
| EAN code | 4007430313720 |
| Working width | 125 mm |
| Cutting depth | 0 - 6 mm // 0 - 1/4 " |
| Torque | 16.8 Nm |
| No-load speed | 750 - 3100 rpm |
| Rated input power | 1900 W |
| Output power | 1240 W |
| Speed at rated load | 2800 rpm |
| Spindle thread | M 14 |
| Weight (without power cable) | 3.8 kg / 8.4 lbs |
| Cable length | 4 m / 13 ft |

Scope of delivery

Bow-type handle, Milling head pointed, Flat-pin spanners, Hexagonal wrench, Plastic carry case