



## MFE 40 with 20 mm diamond cutting disc Universal

- Ideal for electric installations to lay cables and empty pipes under plaster with cutting depths up to 40 mm
- Maximum work progress by means of powerful motor, constant speed and two-speed high-performance gear
- Robust aluminium die-cast hood with rubber rolls and optimal handle position for comfortable guiding of the machine
- Pushing cut for optimal view of the marking line
- Channel width and cutting depth can be set
- Metabo Marathon motor with patented dust protection for long service life
- Tacho-Constamatic (TC)-Full Wave Electronics: fast work progress by means of constant speed under load
- Electronic soft start and restart protection for safe working
- LED signal informs about overload or active restart protection
- Clean, low-dust working by means of connecting a Metabo all-purpose vacuum cleaner (certified with ASR 35 M ACP)
- Suitable for slitting grooves up to a width of 30 mm without centre in one workstep (with special accessories)
- Also suitable for cutting with only one diamond cutting disc
- Metabo S-automatic safety clutch: mechanical decoupling of the drive for safe working should the disc stop unexpectedly

Order no.	604040900
EAN code	4007430333513
Adjustable cutting depth	10 - 40 mm // 3/8 - 1 9/16 "
Possible groove widths	9 / 15.5 / 22 / 28.5 / 35 mm / 3/8 / 5/8 / 7/8 / 1 1/8 / 1 3/8 "
Cutting disc Ø	125 mm / 5 "
Rated input power	1900 W
Output power	1120 W
No-load speed	5000 rpm
Speed at rated load	4200 rpm
Torque	6 Nm / 53 in-lbs
Weight (without power cable)	4.6 kg / 10.1 lbs
Cable length	4 m / 13 ft

### Scope of delivery

Spacer Rings, 2 Diamond cutting discs, 20 mm Diamond channeling disc 2 UP, Flange nut, Face pin wrench, Chase chisel, Plastic carry case