



MARATHON
MOTOR



RSEV 17-125

- For effective spot grinding and removal of concrete, screed and coatings with diamond cup wheels
- Universally applicable system for low-dust grinding indoors and outdoors
- Antistatic extraction hood can be removed without tools for use as angle grinder with guard
- High torque and overload capacity for demanding applications in continuous use
- Fast work progress thanks to powerful, robust Metabo Marathon-motor
- Low weight, ideal for sanding walls and ceilings
- Working close to edges thanks to integrated folding segment
- Vario Tacho Constamatic (VTC) Full-wave Electronics with Thumbwheel: for working at customised speeds to suit the application material and speeds that remain almost constant, even under load
- Electronic soft start for smooth start-up
- Restart protection: prevents unintentional start-up after power supply interruption
- Metabo S-automatic safety clutch: mechanical decoupling of the drive for safe working should the tool stop unexpectedly
- Low-vibration side handle Metabo VibraTech (MVT)
- With metaBOX, the intelligent solution for transport and storage

Order no.	603829510
EAN code	4061792176768

Cup wheel Ø	125 mm / 5 "
No-load speed	2800 - 9600 rpm
Rated input power	1700 W
Output power	1040 W
Speed at rated load	9600 rpm
Spindle thread	M 14
Weight (without power cable)	2.7 kg / 6 lbs
Cable length	4 m / 13 ft

Scope of delivery

Metabo VibraTech (MVT) side handle, Extraction hood GED 125, Inner support flange, Nut with two holes, Diamond cup wheel concrete "classic", Flat-pin spanners, metaBOX 165 L