



## SP 28-50 S Inox

- For drainage and pumping dry of construction pits, cellars and shafts. Also for pumping sewage and waste water in industrial and domestic environments.
- For very coarse dirty water with solid bodies of up to Ø 50 mm
- Double mechanical seal with oil chamber for ideal protection of the pump if the water is very dirty
- Self-cleaning Vortex-impeller to minimise blockages
- Designed for continuous mode with S1 motor operating mode
- Overload protection: protects the motor from overheating
- Float switch for automatic mode
- Suitable for mobile and stationary use thanks to ergonomic handles and stability
- Durable pump housing made of non-corrosive, high-quality stainless steel

| Order no.                   | 604114000                                    |
|-----------------------------|--|
| EAN code                    | 4007430221568                                |
| Rated input power           | 1470 W                                       |
| Maximum delivery rate       | 28000 l/h / 7397 gal/h                       |
| Maximum delivery height     | 12 m / 39 ft                                 |
| Maximum pressure            | 1.2 bar / 17.4 psi                           |
| Maximum immersion depth     | 7 m / 23 ft                                  |
| Discharge port              | 2" female thread                             |
| Pump housing                | Stainless steel                              |
| Protection type IP          | IP 68  |
| Maximum particle size up to | 50 mm / 2 "                                  |
| Number of impellers         | 1  |
| Dimensions                  | 203 x 170 x 537 mm // 8 x 6 11/16 x 21 1/8 " |
| Weight                      | 19.3 kg / 42.5 lbs                           |
| Cable length                | 10 m / 33 ft                                 |

### Scope of delivery

Float switch