



DP 28-10 S Inox

- For effective pumping of large quantities of dirty water, rain water, ground water and water on construction sites
- Ideal motor cooling by means of the conveyed medium even when the water level is low
- Double mechanical seal with oil chamber for ideal protection of the pump if the water is very dirty
- Self-cleaning Vortex-impeller to minimise blockages
- Designed for continuous mode with S1 motor operating mode
- Overload protection: protects the motor from overheating
- Float switch for automatic mode
- Suitable for mobile and stationary use thanks to ergonomic handles and stability
- Durable pump housing made of non-corrosive, high-quality stainless steel

Order no.	604112000
EAN code	4007430221544
Rated input power	1850 W
Maximum delivery rate	28000 l/h / 7397 gal/h
Maximum delivery height	17 m / 56 ft
Maximum pressure	1.7 bar / 24.7 psi
Maximum immersion depth	7 m / 23 ft
Discharge port	1 1/2" female thread
Pump housing	Stainless steel
Protection type IP	IP 68
Maximum particle size up to	10 mm / 3/8 "
Number of impellers	1
Dimensions	215 x 215 x 465 mm // 8 15/32 x 8 15/32 x 18 5/16 "
Weight	18.5 kg / 40.8 lbs
Cable length	10 m / 33 ft

Scope of delivery

Float switch