



## DS 125 M

- Sturdy and compact machine for sharpening, grinding and deburring tasks
- Low-noise and low-vibration, maintenance-free induction motor
- Motor for single phase alternating current
- Workpiece support adjustable without tools
- Large spark protection guards for eye protection
- Vibration-dampening rubber feet for safe support

Order no.	604125000
EAN code	4061792225947
Grinding wheels (Ø x thickness x bore)	125 x 20 x 20 mm // 4 15/16 x 25/32 x 25/32 "
No-load speed	2980 rpm
Mains voltage	220 - 240 V
Rated input power	200 W
Output power	110 W
Breakdown torque	1.1 Nm / 9.7 in-lbs
Weight	6.7 kg / 14.8 lbs
Cable length	1.8 m / 70 7/8 "

### Scope of delivery

Regular aluminium oxide grinding discs 36 P and 60 N, Spark protection glasses, Work piece support