



DG 25 Set

- For sanding/grinding, deburring, moulding/routing and engraving
- Integrated speed control
- Ergonomic, partially rubber-coated housing: cold-insulating, non-slip and low vibration for comfortable work
- Safety lever for protection against accidental start up
- Rotatable exhaust guide at the side of the housing.

Order no.	604116500
EAN code	4007430228918

Operating pressure	6.2 bar / 90 psi
Air requirement	300 l/min / 11 cfm
Maximum speed	25000 rpm
Collet chuck bore	6 mm / 0.2362 "
Weight	0.43 kg / 0.9 lbs

Scope of delivery

EURO Plug-in nipple 1/4", ARO/Orion Plug-in nipple 1/4", ISO Plug-in nipple 1/4", 2 collets (3 mm, 6 mm), 5 mounted points each (3 mm, 6 mm), 2 open-jawed spanners (13 mm, 16 mm), Plastic carry case