



WEA 24-230 MVT Quick with quick-locking nut, rotating main handle

- Metabo Marathon motor with patented dust protection for long service life
- Electronic safety shutdown: reduces kickback if the disc stops unexpectedly - for high user safety
- Reduced vibrations for low-fatigue working thanks to Metabo VibraTech (MVT) damping system and integrated Auto-balancer
- Rotating back handle and side handle can be mounted at 3 positions for optimum handle position also when cutting
- Metabo Quick for tool-free disc change by means of a quick-locking nut
- Tool-free adjustable guard; twist-proof
- Starting current limitation prevents the actuation of the lock on start-up
- Electronic overload protection and restart protection
- Metabo safety switch prevents unintentional start
- Auto-stop carbon brushes to protect the motor
- LED signal indicates triggered restart protection or overheating

Order no.	606472000
EAN code	4007430268259
Disc-Ø	230 mm // 9 "
Rated input power	2400 W
Output power	1600 W
No-load speed	6600 rpm
Speed at rated load	4600 rpm
Torque	17 Nm / 150 in-lbs
Spindle thread	M 14
Handle circumference	144 mm / 5.669 "
Weight (without power cable)	5.9 kg / 13 lbs
Cable length	4 m / 13 ft

Scope of delivery

Guard, Inner support flange, Quick-locking nut, Metabo VibraTech (MVT) side handle