



WVB 18 LT BL 11-125 Quick with brake, speed control, quick-locking nut, rotating battery pack

- Brushless cordless angle grinder of the new generation: as powerful as a 1,100 Watt mains-powered tool thanks to 40% more power
- Service-free Brushless motor with highest efficiency and maximum handiness
- Variable speed setting with thumbwheel for working on materials requiring customised speeds, and at speeds which remain constant under load
- Fast brake system for highest user safety: Disc stops within 1 second after switching off
- M-Quick System for tool-free disc change at the touch of a button
- Tool-free adjustable guard; twist-proof
- Battery pack can be rotated in 90° steps for best ergonomics in any working position
- Metabo S-automatic mechanical safety clutch: minimises kick-back to the lowest level when the disc jams unexpectedly - for maximum user safety
- Electronic overload protection, soft start and restart protection
- Detachable dust protection filter protects motor from coarse particles
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	613057840
EAN code	4061792206601
Battery voltage	18 V
Disc-Ø	125 mm / 5 "
Max. cutting depth	27 mm / 1 1/16 "
No-load speed	2800 - 10000 rpm
Spindle thread	M 14
Handle circumference	191 mm / 7.52 "
Weight without battery pack	1.8 kg
Weight with battery pack	2.5 kg

Scope of delivery

Guard, Inner support flange, M-Quick flange nut, Side handle, Dust protection filter, metaBOX 165 L, without battery pack, without charger