



WEPBA 24-180 MVT Quick with brake, quick-locking nut, rotating main handle, deadman switch

- Metabo Marathon motor with patented dust protection for long service life
- Highest degree of user safety thanks to mechanical disc brake and deadman's switch: disc stop in 2.5 seconds after releasing even in case of a power cut
- Electronic safety shutdown: reduces kickback if the disc stops unexpectedly - for high user safety
- Reduced vibrations for low-fatigue working thanks to Metabo VibraTech (MVT) damping system and integrated Auto-balancer
- Rotating back handle and side handle can be mounted at 3 positions for optimum handle position also when cutting
- Metabo Quick for tool-free disc change by means of a quick-locking nut
- Tool-free adjustable guard; twist-proof
- Starting current limitation prevents the actuation of the lock on start-up
- Electronic overload protection and restart protection
- Metabo safety switch prevents unintentional start
- Auto-stop carbon brushes to protect the motor

Order no.	606480000
EAN code	4007430337658
Disc-Ø	180 mm // 7 "
Rated input power	2400 W
Output power	1600 W
No-load speed	8450 rpm
Speed at rated load	5800 rpm
Torque	14 Nm / 124 in-lbs
Spindle thread	M 14
Handle circumference	149 mm / 5.866 "
Weight (without power cable)	6 kg / 13.2 lbs
Cable length	4 m / 13 ft

Scope of delivery

Guard, Inner support flange, Quick-locking nut, Metabo VibraTech (MVT) side handle