



WPB 18 LT BL 11-125 Quick with brake, quick-locking nut, rotating battery pack, deadman switch

- Brushless cordless angle grinder of the new generation: as powerful as a 1,100 Watt mains-powered tool thanks to 40% more power
- Service-free Brushless motor with highest efficiency and maximum handiness
- Paddle switch with dead man function: safe to operate due to an ergonomically integrated switch
- Fast brake system for highest user safety: Disc stops within 1 second after switching off
- M-Quick System for tool-free disc change at the touch of a button
- Tool-free adjustable guard; twist-proof
- Battery pack can be rotated in 90°steps for best ergonomics in any working position
- Metabo S-automatic mechanical safety clutch: minimises kick-back to the lowest level when the disc jams unexpectedly - for maximum user safety
- Restart protection: prevents unintentional start-up after battery pack change
- Detachable dust protection filter protects motor from coarse particles
- Many brands, one battery pack system: This product can be combined with all 18V battery packs and chargers of the CAS brands: www.cordless-alliance-systems.com

Order no.	613059850
EAN code	4061792206397
Battery voltage	18 V
Disc-Ø	125 mm / 5 "
Max. cutting depth	27 mm / 1 1/16 "
No-load speed	10000 rpm
Spindle thread	M 14
Handle circumference	160 mm / 6.299 "
Weight without battery pack	1.8 kg
Weight with battery pack	2.5 kg

Scope of delivery

Guard, Inner support flange, M-Quick flange nut, Side handle, Dust protection filter, without battery pack, without charger