



WQ 1100-125 with quick-locking nut

- Robust, universal and economical: ergonomic angle grinder for any application
- Powerful motor with good overload capacity
- Tool free, fast disc change at the touch of a button with the Metabo M-Quick-System
- Tool-free adjustable guard; twist-proof
- Metabo S-automatic mechanical safety clutch: minimises kick-back to the lowest level when the disc jams unexpectedly - for maximum user safety and swift progress
- Restart protection after power interruption
- Gear housing can be unscrewed, rotated in 90° steps and re-mounted for left-handed operation or cutting

Order no.	610035000
EAN code	4007430338389
Disc-Ø	125 mm // 4.9 "
Rated input power	1100 W
Output power	700 W
No-load speed	12000 rpm
Speed at rated load	7000 rpm
Torque	3.5 Nm / 31 in-lbs
Spindle thread	M 14
Handle circumference	194 mm / 7 5/8 "
Weight (without power cable)	2.2 kg / 4.9 lbs
Cable length	4 m / 13 ft

Scope of delivery

Guard, Inner support flange, M-Quick flange nut, Side handle