



## SRE 4350 TurboTec

- Excellent sanding finish without scoring marks and grooves, for a professional surface finish
- Oscillating system with double-row angular ball bearing for extremely smooth running and minimum vibration
- Robust clamping system for sanding paper with or without hook and loop fastener, as well as sanding medium up to 10 mm in thickness
- Ball bearing with multiple sealings and tear-proof rubber sleeve protects the machine against aggressive dust
- Side handle with vibration damping for a comfortable grip in any work position
- TurboBoost: allows additional power reserves to be employed for maximum removal
- Vario (V)-Electronics for working at customised orbital frequencies to suit various application materials
- Sanding plate with additional lateral extraction channels for cleaner working
- Dust cartridge with filter for working without connecting to a vacuum cleaner
- Extraction possibility by means of connecting an all-purpose vacuum cleaner

Order no. EAN code	611350000 4007430214218
Base plate	92 x 184 mm (1/3 sheet)
Rated input power	350 W
No-load speed	4200 - 11000 rpm
Orbital frequency with no load	8400 - 22000 rpm
Orbit diameter	2.2 mm / 3/32 "
Weight (without power cable)	2.4 kg / 5.3 lbs
Cable length	4 m / 13 ft

### Scope of delivery

Hook and loop grinding plate, removable side handle, Textile dust bags