



RWEV 1200-2

- Universal two-speed stirrer for comfortable stirring and mixing up to 50 litres
- Minor effort to guide the stirrer thanks to ergonomically favourable handle position
- Rubber corners at the housing for effective protection from damage, safe storage and non-slip leaning against a wall
- The side cable exit reduces the risk of a cable break
- High torque thanks to two-speed gear for viscous materials
- Robust die cast aluminium gear housing for optimum heat dissipation and durability
- Splash-water proof motor cover to protect against dirt, mud and splash water
- Electronic soft start for splash-free working
- Vario-Tacho-Constamatic (VTC)-Full Wave Electronics for work with materials requiring customised speeds, which remain constant under load
- Thumbwheel for speed preselection

Order no.	614049000
EAN code	4061792221505
Rated input power	1200 W
Output power	600 W
No-load speed	0 - 300 / 0 - 650 rpm
Gears	2
Maximum stirring paddle diameter	140 mm / 5 1/2 "
Max. recommended mixing amount	50 l
Bit retainer	Female thread M 14
Collar diameter	50 mm / 1 31/32 "
Weight (without power cable)	4.3 kg
Cable length	4 m / 13 ft

Scope of delivery

Stirrer paddle RS-R3 (Ø 140 mm), Open-jawed spanner