



PE 15-25 Set

- Renovation set with powerful polisher for restoration of beams of half-timbered houses and for restructuring wood
- Maximum productivity thanks to powerful 1,500 Watt motor and high-performance planetary gear train
- Vario-Tacho-Constamatic (VTC)-Full Wave Electronics with Thumbwheel: for working at customised speeds to suit the application material and speeds that remain almost constant, even under load
- Tool-free adjustable bow-type handle for safe and uniform guidance when working
- Overload protection: protects the motor from overheating
- Electronic soft start for smooth start-up
- Restart protection: prevents unintentional start-up after power supply interruption
- Auto-stop carbon brushes to protect the motor
- With metaBOX, the intelligent solution for transport and storage

Order no.	615250500
EAN code	4007430324191
For backing pad up to maximum	180 mm / 7 "
Rated input power	1500 W
Output power	870 W
No-load speed	700 - 2500 rpm
Speed at rated load	2250 rpm
Torque	18 Nm / 159 in-lbs
Spindle thread	M 14
Weight (without power cable)	2.4 kg / 5.3 lbs
Cable length	4 m / 13 ft

Scope of delivery

Side handle, Safety goggles, 3 Disc brushes (130 mm; P46, P60, P80), metaBOX 165 L