



## WEPF 9-125 Quick

- Most compact flat-head angle grinder for working at acute angles down to 43°
- Particularly developed for the removal of weld slag, rust or paint in narrow frame constructions and for working in tight spaces
- Metabo Marathon motor with patented dust protection for long service life
- Constamatic (C)-Full wave electronics: fast work progress by means of almost constant speed under load
- Metabo Quick for tool-free disc change by means of a quick-locking nut
- Tool-free adjustable guard; twist-proof
- Paddle switch with deadmans function: safe to operate due to an ergonomically integrated non-slip switch
- Electronic safety shutdown: reduces kickback if the disc stops unexpectedly - for high user safety
- Electronic overload protection, soft start and restart protection
- Auto-stop carbon brushes to protect the motor

Order no.	613069000
EAN code	4007430240743
Minimum accessible angle	43 °
Disc-Ø	125 mm / 5 "
Rated input power	910 W
Output power	430 W
No-load speed	10500 rpm
Speed at rated load	8200 rpm
Torque	2 Nm / 18 in-lbs
Spindle thread	M 14
Weight (without power cable)	2.1 kg / 4.6 lbs
Cable length	4 m / 13 ft

### Scope of delivery

Guard, Inner support flange, Quick-locking nut, Side handle, 1 Flap disc Flexiamant Super Convex (125mm; P60)