



## WEVF 10-125 Quick Inox

- The most easy-to-handle flat-head angle grinder with speed regulation for perfect processing of stainless steel e.g. railings and hand rails
- Particularly developed for the removal of weld slag, rust or paint in narrow frame constructions and for working in tight spaces
- Longer service life, more power: the Metabo Marathon-motor with patented dust protection, up to 20% more overload capacity and 50% more torque
- Thumbwheel controlled Vario-Constamatic (VC)-Full wave electronics ideal for working on materials requiring customised speeds, and at speeds which remain almost constant under load
- Metabo Quick for tool-free disc change by means of a quick-locking nut
- Tool-free adjustable guard; twist-proof
- Electronic safety shutdown: reduces kickback if the disc stops unexpectedly - for high user safety
- Electronic overload protection, soft start and restart protection
- Gear housing can be unscrewed, rotated in 90° steps and re-mounted for left-handed operation or cutting
- Auto-stop carbon brushes to protect the motor

Order no.	61308000
EAN code	4007430275677
Minimum accessible angle	43 °
Disc-Ø	125 mm / 5 "
Rated input power	1000 W
Output power	590 W
No-load speed	2000 - 7600 rpm
Speed at rated load	6300 rpm
Torque	3.5 Nm / 31 in-lbs
Spindle thread	M 14
Weight (without power cable)	2.3 kg / 5.1 lbs
Cable length	4 m / 13 ft
Handle circumference	193 mm / 7.594 "

### Scope of delivery

Guard, Inner support flange, Quick-locking nut, Side handle, 1 Flap disc Flexiamant Super Convex (125mm; P60)