



Flexiamant super 300x3.0x25.4 stone, cutting disc, straight type

- Universal use for processing natural and artificial stone
- Also suitable for processing non-ferrous metals
- Hardness: hard
- High cutting output with long tool life
- Maximum working speed 100 m/s
- For powerful machines (machine load > 5 KW)

Order no.	616212000
EAN code	4007430400871
Quality class	C 30-S
Diameter x thickness x bore	300 x 3 x 25.4 mm
Version	straight
Maximum speed	6365 rpm
Sales unit / packaging unit	1 / 10