



## Flexiamant super 400x3.0x25.4 steel, cutting disc, straight type

- High cutting output with good tool life in steel
- Soft version for less powerful machines (machine load < 3 KW)
- Maximum working speed 80 m/s

<b>Order no.</b>	<b>616215000</b>
<b>EAN code</b>	<b>4007430400918</b>
Quality class	A 24-M
Diameter x thickness x bore	400 x 3 x 25.4 mm
Version	straight
Maximum speed	3820 rpm
Sales unit / packaging unit	1 / 10