



Flexiamant super 180x6.0x22.23 steel, grinding disc, offset type

- Universal disc for all metal processing requirements
- Especially suitable for deburring and grinding edges, also for cast processing
- Hardness: hard
- Good cutting output with extremely good tool life
- Maximum working speed 80 m/s

Order no.	616277000
EAN code	4007430061485
Quality class	A 24-T
Diameter x thickness x bore	180 x 6 x 22.23 mm
Version	offset
Maximum speed	8500 rpm
Sales unit / packaging unit	1 / 10