



Flexiamant super 300x3.5x22.2 steel, cutting disc, straight type

- For use in all steel processing applications, also for cast materials
- Hardness: medium
- High cutting output with long tool life
- Maximum working speed 80 m/s
- Cutting discs with 2 reinforced fabrics due to the increased side load with petrol cutters

Order no.	61613500
EAN code	4007430400338
Quality class	A 24-N
Diameter x thickness x bore	300 x 3.5 x 22.2 mm
Version	straight
Maximum speed	5090 rpm
Sales unit / packaging unit	1 / 10