



Flexiamant super 350 x 3.0 x 25.4 steel, cutting disc, straight type

- High cutting output with good tool life in steel
- Soft version for less powerful machines (machine load < 3 KW)
- Maximum working speed 80 m/s

Order no.	616338000
EAN code	4007430401595
Quality class	A 24-M
Diameter x thickness x bore	350 x 3 x 25.4 mm
Version	straight
Maximum speed	4365 rpm
Sales unit / packaging unit	1 / 10