



## Flexiamant super 350 x 3.0 x 25.4 Inox, cutting disc, straight type

- Medium-hard special cutting disc for stainless steel
- High cutting output with good tool life
- Low in iron and sulphur <0.1%
- Maximum working speed 80 m/s
- Medium-hard version for less powerful machines (machine load <3 KW)
- Suitable for stainless steels

|                  |                      |
|------------------|----------------------|
| <b>Order no.</b> | <b>616343000</b>     |
| <b>EAN code</b>  | <b>4007430128836</b> |

|                             |                   |
|-----------------------------|-------------------|
| Quality class               | A 36-R            |
| Diameter x thickness x bore | 350 x 3 x 25.4 mm |
| Version                     | straight          |
| Maximum speed               | 4365 rpm          |
| Sales unit / packaging unit | 1 / 10            |