



Novoflex 100x6.0x16.0 steel, grinding disc, offset type

- Quality Novoflex: powerful entry-level class
- Hardness: medium-hard
- Universal use in metal processing
- Good cutting output with good tool life
- Maximum working speed 80 m/s

Order no.	616429000
EAN code	4007430122742
Quality class	A 24
Diameter x thickness x bore	100 x 6 x 16 mm
Version	offset
Maximum speed	15300 rpm
Sales unit / packaging unit	1 / 25