



Flexiamant 180x3.0x22.23 Inox, cutting disc, straight type

- Universal disc for processing stainless steels
- Hardness: soft
- High cutting output with long tool life
- Low in iron and sulphur <0.1%
- Maximum working speed 80 m/s

Order no.	616163000
EAN code	4007430400666
Quality class	A 30-P
Diameter x thickness x bore	180 x 3 x 22.23 mm
Version	straight
Maximum speed	8500 rpm
Sales unit / packaging unit	1 / 25