



**Cup wheel 110/90x55x22.23 A 16 Q, steel,
tapered type, pack: 1 piece**

- Surface grinding in the entire metal area with angle grinders
- Hardness: hard
- Resin-bonded
- Good cutting output with good tool life
- Maximum working speed 50 m/s
- For angle grinders with grinding wheel Ø 180 mm and 230 mm

Order no.	61617000
EAN code	4007430400680

Diameter x thickness x bore	110 x 55 x 22.23 mm
-----------------------------	------------------------

Maximum speed	8600 rpm
---------------	----------

Sales unit / packaging unit	1 / 6
-----------------------------	-------