



## Combinator 115x1.9x22.23 mm, Inox, cutting and grinding disc, offset version

- One grinding wheel for two applications: quick cutting, as well as easy deburring and sanding
- All-purpose use for processing stainless steel and for general metal processing
- Low in iron, sulphur and chlorine (Fe + S + Cl ≤ 0.1 %)
- Hardness: hard
- Reduces labour costs by saving on set-up time
- Eliminates time-consuming disc change during mobile use
- Highest standards in quality and safety thanks to the dimensional and lateral stability of the disc design (proven safety with 3 full-surface layers of material)
- Maximum working speed: 80 m/s

<b>Order no.</b>	<b>61650000</b>
<b>EAN code</b>	<b>4007430186911</b>
Quality class	A 46-U Combinator Inox
Diameter x thickness x bore	115 x 1.9 x 22.23 mm // 4 1/2 x 1/16 x 7/8 "
Version	offset
Maximum speed	13200 rpm
Sales unit / packaging unit	1 / 25