



Cup wheel 110/90x55x22.23 C 16 N, stone, tapered type, pack: 6 pieces

- For rough work, even for cast iron
- Resin-bonded
- Good cutting output with good tool life
- Surface grinding across the entire stone processing sector
- Also suitable for cast iron materials and non-ferrous metals
- Maximum working speed 50 m/s
- For angle grinders with grinding wheel Ø 180 mm and 230 mm
- Hardness: medium-hard

Order no.	616171000
EAN code	4007430400697

Diameter x thickness x bore	110 x 55 x 22.23 mm
-----------------------------	---------------------

Maximum speed	8600 rpm
---------------	----------

Sales unit / packaging unit	1 / 6
-----------------------------	-------