



Flexiamant super 300x3.0x25.4 steel, cutting disc, straight type

- Universal use in metal processing
- Hardness: hard
- High cutting output with long tool life
- Maximum working speed 100 m/s
- For powerful machines (machine load > 5 KW)
- 616203000: 350x3.5x25.4mm: Also suited for cutting railway tracks

Order no.	616202000
EAN code	4007430400826
Quality class	A 30-S
Diameter x thickness x bore	300 x 3 x 25.4 mm
Version	straight
Maximum speed	6365 rpm
Sales unit / packaging unit	1 / 10