



Flexiamant super 350 x 3.0 x 25.4 steel, cutting disc, straight type

- Good cutting output with good tool life in steel
- Hard version for powerful machines (machine load > 3 KW)
- A 36-S: with an inside gauze for quick cuts
- Maximum working speed 80 m/s

Order no.	616339000
EAN code	4007430109132
Quality class	A 36-S
Diameter x thickness x bore	350 x 3 x 25.4 mm
Version	straight
Maximum speed	4365 rpm
Sales unit / packaging unit	1 / 10