



## Novorapid 150 x 1.6 x 22.23 mm, steel, cutting disc, form 41

- Quality Novorapid: powerful entry-level class
- Thin cutting disc for general metal processing, especially for thin-walled materials such as pipes, metal sheets, profiles, wires etc.
- Good cutting performance with good tool life.
- Hardness: medium-hard
- Low material consumption, power-saving, low machine load
- Maximum working speed: 80 m/s

<b>Order no.</b>	<b>61650700</b>
<b>EAN code</b>	<b>4007430248022</b>
Quality class	A 46-R
Diameter x thickness x bore	150 x 1.6 x 22.23 mm // 6 x 0.06 x 7/8 "
Version	straight
Maximum speed	10200 rpm
Sales unit / packaging unit	1 / 25