



Flexiamant 355x3.0x25.4 steel, cutting disc, shape 41

- For use in all steel processing applications
- High cutting output with good tool life
- Uniform in cutting output and tool life
- Soft version for less powerful machines (machine load <3 KW)
- Maximum working speed 80 m/s

Order no.	61634600
EAN code	4061792188631
Quality class	A 30-R
Diameter x thickness x bore	355 x 3 x 25.4 mm // 14 x 0.12 x 1 "
Version	straight
Maximum speed	4365 rpm
Sales unit / packaging unit	1 / 10