



Flexiamant super 100x6.0x16.0 Inox, grinding disc, offset type

- Special disc for processing stainless steels
- Low in iron and sulphur <0.1%
- Hardness: soft
- Very good cutting output with good tool life
- Maximum working speed 80 m/s

Order no.	616735000
EAN code	4007430435125
Quality class	A 36-O
Diameter x thickness x bore	100 x 6 x 16 mm
Version	offset
Maximum speed	15300 rpm
Sales unit / packaging unit	1 / 25