



Flexiamant 100x6.0x16.0 steel, grinding disc, offset type

- Universal disc for all metal processing requirements
- Hardness: medium
- High cutting output with long tool life
- Maximum working speed 80 m/s

Order no.	61674500
EAN code	4007430403230
Quality class	A 24-N
Diameter x thickness x bore	100 x 6 x 16 mm
Version	offset
Maximum speed	15300 rpm
Sales unit / packaging unit	1 / 25