



Novorapid 115 x 1.0 x 22,23 mm, steel, cutting disc, form 41

- Quality Novorapid: powerful entry-level class
- Thin cutting disc for general metal processing, especially for thin-walled materials such as pipes, metal sheets, profiles, wires etc.
- Good cutting performance with good tool life.
- Hardness: medium-hard
- Low material consumption, power-saving, low machine load
- Maximum working speed: 80 m/s

Order no.	61650500
EAN code	4007430248565
Quality class	A 60-R
Diameter x thickness x bore	115 x 1 x 22.23 mm // 4 1/2 x 0.04 x 7/8 "
Version	straight
Maximum speed	13300 rpm
Sales unit / packaging unit	1 / 25