



## Flexiamant 180x6.0x22.23 steel, grinding disc, offset type

- Universal disc for all metal processing requirements
- Hardness: medium
- High cutting output with long tool life
- Maximum working speed 80 m/s

<b>Order no.</b>	<b>616560000</b>
<b>EAN code</b>	<b>4007430402424</b>
Quality class	A 24-N
Diameter x thickness x bore	180 x 6 x 22.23 mm
Version	offset
Maximum speed	8500 rpm
Sales unit / packaging unit	1 / 10