



Flexiamant 115x6.8x22.23 steel, grinding disc, offset type

- Universal disc for all metal processing requirements
- Hardness: medium
- High cutting output with long tool life
- Maximum working speed 80 m/s

Order no.	616725000
EAN code	4007430445094
Quality class	A 24-N
Diameter x thickness x bore	115 x 6.8 x 22.23 mm
Version	offset
Maximum speed	13300 rpm
Sales unit / packaging unit	1 / 25