



## Flexiamant super 125x2.5x22.23 aluminium, cutting disc, straight type

- Universal disc with open structure for processing non-ferrous metals such as aluminium, copper, brass, bronze ...
- Hardness: soft
- High cutting output with long tool life
- Maximum working speed 80 m/s
- Attention: Good extraction is obligatory in closed rooms, as highly concentrated aluminium dust can lead to explosions!

<b>Order no.</b>	<b>616752000</b>
<b>EAN code</b>	<b>4007430403339</b>
Quality class	A 30-O
Diameter x thickness x bore	125 x 2.5 x 22.23 mm
Version	straight
Maximum speed	12200 rpm
Sales unit / packaging unit	1 / 25