



Flexiamant 115x2.5x22.23 Inox, cutting disc, offset type

- Universal disc for processing stainless steels
- Hardness: soft
- High cutting output with long tool life
- Low in iron and sulphur <0.1%
- Maximum working speed 80 m/s

Order no.	616737000
EAN code	4007430403100
Quality class	A 30-P
Diameter x thickness x bore	115 x 2.5 x 22.23 mm
Version	offset
Maximum speed	13300 rpm
Sales unit / packaging unit	1 / 25