



**Cup brush 75x0.3 mm/ M 14, steel-wire,  
crimped, wire thickness 0.30 mm**

- For light surface processing and deburring work in all metal processing
- For processing larger areas, weld seams, metal plates
- Edging type: crimped steel wire

<b>Order no.</b>	<b>623715000</b>
<b>EAN code</b>	<b>4007430407801</b>
Diameter	75 mm
Female thread	M 14
Wire thickness	0.30 mm
Maximum speed	11000 rpm
Sales unit / packaging unit	1 / 1