



## HSS bi-metal hole saw, Ø 60mm

- Hole saws made of bi-metal with hardened cobalt teeth. Quicker chip removal through a new kind of teeth with irregular tooth shape and division; giving much quicker cuts with less vibration. The larger teeth gaps and the inclination ensure effective chip removal.
- Quicker and softer chip removal through new kind of teeth with irregular tooth shape and division; thus less vibration
- For use in cast steel and grey cast iron, stainless steel, constructional steel, aluminium, bronze, copper, PVC, acrylic glass, wood.
- Maximum cutting depth about 35 mm
- Thread for hole saws-Ø 14-30 mm: 1/2"-20 UNF; thread for hole saws-Ø 32-152mm: 5/8"-18 UNF
- Use hole saws only with the corresponding arbor and pilot drill.

Order no.  
EAN code

62519000  
4007430103161

Diameter

60 mm / 2 3/8 "